

# NABÍDKA PRODUKTŮ



**EMC<sup>2</sup>**  
 where information lives
**34550 - StorCenter Pro ix4-200d NAS Server, 4.0TB****Cena: 19 650 Kc bez DPH**

- ▶ Marvell 6281@1.2GHz & 512MB RAM
- ▶ 2 x GigE & 3 x USB
- ▶ Blue LCD - 4 x Swappable HDDs
- ▶ RAID 0, 10, 5 & JBOD with Auto rebuild
- ▶ HDD spin down, Energy Star
- ▶ iSCSI, NAS-to-NAS File Replication
- ▶ QuikTransfer button to USB disks
- ▶ CIFS, NFS, AFP, FTP, SNMP
- ▶ DLNA Certified AV media server
- ▶ Time Machine, iTunes, PTP, Bluetooth
- ▶ ADS support, Print Server, UPS
- ▶ 11-language support
- ▶ QuikProtect & Retrospect & MozyHome
- ▶ 3 years Warranty

**34543 - StorCenter Pro ix4-200r NAS Rackmount Server, 4.0TB****Cena: 55 360 Kc bez DPH**

- ▶ Intel® Celeron D 352 @ 3.2GHz
- ▶ 1GB DDR2 RAM, Gigabit Ethernet ; 3 x USB
- ▶ RAID 5,10 & JBOD
- ▶ 4 x Hot Swap & Auto RAID Rebuild
- ▶ ADS support (users & groups)
- ▶ Disk quotas per folder
- ▶ UPS support
- ▶ Very Cost effective @ Top performance
- ▶ Very slim, 1U form factor
- ▶ Very easy to use & administer
- ▶ iSCSI, NAS-to-NAS remote replication,
- ▶ One-touch NAS-to -Disk backup
- ▶ VMware®Certified: HCL certified iSCSI and NAS (NFS) storage for VMware
- ▶ Windows®Certified: Certified for Windows Server 2003 and 2008, including Hyper-V
- ▶ XenServer®Certified: HCL certified for Citrix XenServer
- ▶ Microsoft (CIFS/SMB/Rally), FTP, Linux/UNIX (NFS), HTTP, Apple AFP / Bonjour support, SNMP
- ▶ 3 years Warranty


**iomega**  
 an EMC company
**Bližší informace:****Petr Flek****Tel.: 602 710 392****[petr.flek@avnet.com](mailto:petr.flek@avnet.com)**