

Accelerating Your Success™



Lieferprogramm

März 2009



Der Partner, dem **Profis** **vertrauen**



Unter dem Dach der Avnet Inc. vermarktet und vertreibt Avnet Technology Solutions IT-Produkte und Lösungen führender Computerhersteller mit Niederlassungen in 34 Ländern. Als weltweites Technologieunternehmen verfügt Avnet Technology Solutions über spezialisierte Vertriebs- und Marketingbereiche, die sich auf spezifische Kundensegmente und eine ausgewählte Line-card konzentrieren und somit auf die Bedürfnisse ihrer Kunden und Lieferanten in besonderem Maße eingehen können.

Das Angebot umfasst Produkte und Lösungen aus den Bereichen:

- Computer Components
- Display Solutions
- Document Management Technologies
- Embedded Computing
- Networking & Security
- Server & Infrastructure Solutions
- Server Based Computing / Thin Clients
- Services
- Software
- Storage & SAN
- Unified Communications
- Virtualisation
- Wireless & Mobility

Als führendes Value Added Distributionsunternehmen von IT-Produkten und Services verschaffen wir unseren Geschäftspartnern Zugang zu einer breiteren Kundenbasis und bieten individuelle Lösungen an. Unser umfangreiches Serviceangebot und unsere langfristigen Partnerschaften mit führenden Technologieanbietern stellen sicher, dass unsere Geschäftspartner das erforderliche Know-how sowie die nötigen Ressourcen erhalten, um neue Geschäftsfelder erfolgreich zu erschließen.

Zu unseren Kunden zählen

- Value-Added Resellers (VARs)
- Independent Software Vendors (ISVs)
- Original Equipment Manufacturers (OEMs)
- System- und Netzwerkintegratoren
- Systemhäuser

Avnet Technology Solutions ist ein operativer Geschäftsbereich der Avnet, Inc. (NYSE:AVT) mit einem Jahresumsatz von 7,63 Milliarden US-\$ im Geschäftsjahr 2008, das am 30. Juni 2008 endete.

Avnet Inc. – Das Unternehmen in Zahlen

Fortune 500 (Platz 163 im Jahr 2008)
Jahresumsatz: 17,95 Mrd. US Dollar in 2008
Börse: NYSE:AVT
Handelsregistereintragung: 1955
Börseneinführung: 1959
CEO: Roy Vallee
Hauptverwaltung: Phoenix, Arizona
Tätig in 70 Ländern
300 Niederlassungen weltweit

Communication

Motorola/Emerson
Communication Boards

Serial Communication

Control Europe
Multiportkarten
Serielle Hubs

Computer Components

Chenbro
Server-/Workstation-Chassis
Rackmount-Chassis

Controller

3ware/AMCC
High Performance 3GB/s Serial Attached SCSI (SAS) RAID Controller
3ware Serial ATA (SATA), 3Gb/s SATA II and ATA RAID Controller
PCI-X to Serial ATA II RAID Controller
PCI Express 3Gb SATA over 800MB/sec RAID 5 reads and exceed 380MB/sec RAID 5 writes
StorSwitch non-blocking switch fabric technology

CPUs

AMD
Athlon64
Athlon Phenom
Sempron
Opteron
Turion
Mobile-CPUs

Graphic Cards

Matrox
Grafikkarten PCI-Bus
Grafikkarten AGP-Bus
Grafikkarten-Zubehör

Sapphire
Grafikkarten PCI-Bus
Grafikkarten PCI-Express
Grafikkarten AGP-Bus

XFX
Grafikkarten PCI-Bus
Grafikkarten PCI-Express
Grafikkarten AGP-Bus

Harddisks

Hitachi
Desktop-HDDs
SATA-HDDs
SAS-HDDs
SCSI-HDDs
Mobile-HDDs

Seagate/Maxtor
Desktop-HDDs
SATA-HDDs
SCSI-HDDs
Fibre Channel HDDs
Mobile-HDDs
External-HDDs
SAS-HDDs

Toshiba
Mobile-HDDs

Mainboards

BCM
Revisionskontrollierte Hauptplatinen mit langer Produktverfügbarkeit und ATX, MicroATX, Mini-ITX, 3.5" & 5.25" EBC und System on Module
Formfaktor

Intel
Mainboards
Zubehör

Itox
Revisionskontrollierte Hauptplatinen mit langer Produktverfügbarkeit und ATX, MicroATX, Mini-ITX und FlexATX Formfaktor

Motorola/Emerson
VME
CompactPCI CPU Platinen basierend auf Intel und PowerPC Architektur
DSP Platinen
drahtlose Datenpakete/Sprachanwendungsplatinen

Supermicro
Mainboards, Zubehör

Tyan
Mainboards
Zubehör

Memory

A-DATA

Kingston

Micron

Samsung

Transcend
Arbeitsspeicher
Flash
SSD
externe Festplatten
Speichermedien mit industriellen Spezifikationen
MP3/MP4-Player

Optische Laufwerke

LG

Display Solutions

Chi Mei
7" und 19" TFT LCD Displays
20" bis 47" TV TFT LCD Displays

IDTech
12.1" bis 22" TFT LCD Displays
Bildauflösung bis 9 Mio. Pixel bei 22"

Nanya
CSTN-LCD Displays
STN-LCD Displays inkl. TAB und COG Technologie
kundenspezifische LCD Displays

Powertip
STN-LCD Displays
kundenspezifische LCD Displays

Sharp
3.5" bis 37" TFT LCD Displays
CSTN LCD Displays

Monitore

EIZO
Office und Color Graphic Monitore
Medical Monitore

Document Management Technologies

Dokumentenscanner

Böwe Bell & Howell

Canon

Fujitsu

Kodak

Panasonic

Scan-Optics

Visioneer

Netzwerkprodukte für Document Management

Fujitsu
Netzwerkbox für fi-Scanner

Silex Technology
USB und Serielle Device Server
Print Server
Ethernet Konverter

Netzwerkscanner für Document Management

Canon

Fujitsu

Kodak

Software for Document Management

eCopy

Software zur Anbindung von MFPs und Scannern an DMS Systeme

EMC-Captiva

Capture Software
ISIS-Treiber

Kodak

Capture Software

Kofax

Bildverbesserungssoftware

NSi

Capture Middleware Anbindung von Scannern, Netzwerk-scannern und MFPs
Schnittstellen zu DMS Systemen und MS Sharepoint

Networking & Security

Enterasys Networks

A-, B-, C-, D-, G-, I-, S-Series
Matrix E1, E7,
N1, N3, N5, N7
Series Router
XSR Security WAN Routers
- Atlas Network
Management Software
Wireless Roamabout
Wireless Switching
Intrusion Detection Security (Dragon)
NAC, Lancare Wartungs- und Servicepakete

Expand Networks

WAN Optimisation

F5 Networks

Local Traffic Management Solutions
Global and Link Traffic Management Solutions
Data Solutions (ARX)
Application Security Solutions
WAN Optimisation & Application Acceleration Solutions
SSL VPN Solutions
Enterprise Management Solutions
Installation Services
Consulting Services
Training Services
Service and Support

Transition Networks

Point System
Standalone Converter
Multiport Converter
Conversion Center
Transceiver/NICs
Hubs
Repeater
Baluns
Milan Switches
Industrieswitche
Optical Networks

Wireless Networking

Honeywell

Intermec

Motorola Enterprise Mobility (Symbol)
WLAN Accesspoints
Handheld Terminals mit WLAN

Ruckus Wireless

Wireless Switching
Zone-, Metro-, Mediaflex
Flexmaster

Trapeze Networks

Wireless Switching
Mobility Exchange
Mobility Points
Ringmaster
Location Appliances

Server & Infrastructure Solutions

HP

HP Integrity Server
HP 9000 Server
HP Superdome
HP ProLiant Server
HP Blade System

IBM

IBM Power Systems (System i)
IBM Power Systems (System p)
IBM System x
BladeCenter Solutions
IBM ePac
IBM Services

Intel

kundenspezifische Server für Applikationen, Telekom, Automation, etc.

Motorola/Emerson

Telekommunikationsserver

Supermicro

Intel processor-based Server
AMD processor-based Server

Tyan

Intel processor-based Server
AMD processor-based Server
Barebones

Certified Server Memory

Kingston

Samsung

Printing Solutions

InfoPrint Solutions Company

CutSheet
MatrixLinePrinter
MatrixPrinter
WorkgroupLaserprinter
ThermoPrinter
InfoPrinter

Server Based Computing

Chip PC

Thin Clients

Ericom

Zugriffssoftware für WTS- und Legacy-Host-Systeme

H+H Software

NetMan Desktop Manager

Samsung

Integrierte Thin Clients

ThinPrint

print engine for terminal services

UniCon

UniCon eLux – Thin Client Betriebssystem
UniCon Scout Enterprise – Management Software für Thin Clients mit eLux

VXL

Thin Clients
Thin Client Notebooks

Wyse

Thin Clients
Thin Client Notebooks

Software

Brocade

SAN Management Software

Ericom

Server Based Computing

Esker

Terminalemulation TUN/Smarterm

H+H Software

NetMan Desktop Manager (NDM)
- Programm zur Bereitstellung und zum Management von Anwendungssoftware in einer Terminalserver-Umgebung

HP

HP IT Management Software:
Strategie:
- Project & Portfolio Management Center
- SOA Center
Applikationen:
- Quality Center
- Performance Center
- Application Security Center
Betrieb:
- Business Availability Center
- Operations Center
- Network Management Center
- Client Automation Center
- Data Center
- Service Management Center
HP Storage Software:
- HP DataProtector
- HP Data Protector Express
- HP Storage Essentials
HP Virtualisierungssoftware:
- VMware
HP Software für Betriebssysteme:
- RedHat Linux
- Novell Linux
- HP Reseller Option Kit für Microsoft Windows Server

HP / Lefthand

Storage Virtualisierung für HP, IBM, VMware
iSCSI Storage Software für HP und IBM

IBM

IBM Lotus:
 - Messaging
 (Notes, Domino, Sametime)
 - Office Applikationen
 (Symphonie)
 - Dokumentenmanagement
 (Quickr)
 - Portale
 - elektronische Formulare
 IBM WebSphere:
 - Business Process Management
 - Application Server
 - SOA
 - eCommerce
 IBM Tivoli:
 - Sicherheitsmanagement
 - Storage Management
 - Service Management
 - Asset Management
 IBM Information Management:
 - Datenbanken
 - Business Intelligence
 - Content Management
 - Archivierung
 IBM Rational:
 - Softwareentwicklung
 - Softwarequalität

Motorola/Emerson

FACT – telekomspezifische
 Software

QStar

Storage Management
 HSM und Hochverfügbarkeits-
 lösungen für Raid, MO, UDO,
 DVD, BD und Tape

StorLife

Content Adressed Storage
 Hardware unabhängige CAS
 Lösungen

tecmasters

Active Repository Manager
 Mangementsoftware für MS
 SharePoint in Verbindung mit CAS

UniCon

UniCon eLux – Thin Client
 Betriebssystem
 UniCon Scout Enterprise –
 Management Software für Thin
 Clients mit eLux

Storage**Chenbro**

Storage Server Chassis

IBM

IBM Enterprise Storage Server
 IBM Enterprise Libraries
 IBM NSeries
 IBM Tape Drives
 IBM Disk Storage
 IBM Switche (Brocade, McData)

QStar**Archive Solutions****iTernity**

HP iCAS Appliances

GRAU DATA

Filelock
 Archivmanager

Storage Appliances

True Worm Speicherlösungen

QStar

SntryML - Emailarchivierung
 Storage Appliances
 Stagemanagement Appliances
 für MO, UDO, DVD, BD und Tape

Backup Solutions**BakBone**

Backup-Lösungen
 Disaster Recovery-Lösungen

Dot Hill**HP**

HP StorageWorks Tape Libraries
 HP StorageWorks
 Autoloader
 StorageWorks Data
 Protection Storage
 Server

NetApp

Backup-to-Disk
 Virtual Tape Libraries (VTL)

Quantum (Adic)

Autoloader
 Libraries
 Backup-to-Disk-Lösungen (VTL)
 und Medien

Network Attached Storage**Brocade**

File Area Network Lösungen
 Wide Area Network Lösungen

HP

HP StorageWorks NAS Systeme

NetApp

NAS und iSCSI

Overland

SNAP NAS und
 iSCSI Server

Storage Arrays**3ware/AMCC**

3ware Serial ATA (SATA), 3Gb/s
 SATA II and ATA RAID Controller
 PCI-X to Serial ATA II RAID
 Controller
 PCI Express 3Gb SATA over
 800MB/sec RAID
 5 reads and exceed 380MB/sec
 RAID 5 writes
 StorSwitch non-blocking switch
 fabric technology

Dot Hill**FibreNetix**

SAS und SATA Raid-
 Systeme
 SCSI oder FC Interconnect

HP

HP StorageWorks SCSI Arrays
 HP StorageWorks Fibre Channel
 Arrays

HP / Lefthand

iSCSI SAN Controller
 Open iSCSI SAN

IBM

IBM Enterprise Storage-Server
 IBM Disk Storage-Server

NetApp

Fibre Channel Arrays
 Fibre Channel Gateways
 (V-Series)

Storage Management**Decru/NetApp**

Storage Security
 Absicherung heterogener
 Storage Devices

HP

HP System Management
 HP Integrity Essentials
 HP ProLiant Essentials

IBM

IBM Tivoli Storage Manager

NetApp

IS1200 ILM-Lösungen
 Virtual File Management
 Management Applications

Storage Networking**Alacritech**

TOE & iSCSI HBAs

Bridgeworks

Bridges & Routers

Brocade

Fabric Switches
 Director / Core Fabric Switches
 Bridges & Routers
 IP Storage Switches
 Wide Area File Services
 Storage Management Software
 SAN Extension and Routing

Cisco

Fabric Switches
 Director / Core Fabric Switches
 IP Storage Switches
 SAN Extension and Routing

Crossroads

Bridges & Routers

Emulex

Fibre Channel HBAs
 Bridges & Routers
 Intelligent Fabrics

Neterion

TOE & iSCSI HBAs

NTP Software

Storage Management Software

QLogic

Fabric Switches
 Fibre Channel HBAs
 TOE & iSCSI HBAs
 Intelligent Fabrics
 InfiniBand
 SAN Extension and Routing

SmartOptics

Transceivers
Cables
Accessories

Xsigo Systems

Director / Core Fabric Switches

Tape Drives

HP

Tape Drives LTO/SDLT

IBM

Tape Drives LTO/Library

Quantum (Adic)

Einzelaufwerke
Autoloader
Libraries
Backup-to-Disk-Lösungen (VTL)
und Medien

Tape Media

Fuji

DLT/SuperDLT/LTO

HP

DLT/Super DLT/DAT/LTO

Quantum (Adic)

DLT/SuperDLT/LTO

Virtualisation

Applikationsvirtualisierung

Ericom

Wyse

Storage-Virtualisierung

HP / Lefthand

HP VSE

IBM

NetApp

Netzwerk-Virtualisierung

Enterasys

Wireless & Mobility

Honeywell

Intermec

**Motorola Enterprise Mobility
(Symbol)**

Printing Solutions

Datamax

Intermec

O'Neil

Barcode-Drucker
Spezialdrucker

Scanner

Honeywell

Intermec

**Motorola Enterprise Mobility
(Symbol)**

CCD und Laser Scanner
Decoder
Lesestifte
inkl. und exkl. drahtlose
Übertragungstechnologie (WLAN)
OEM Scan Engines

Avnet Technology Solutions –

Partner der Besten

3ware/AMCC

A

ABBYY

A-DATA

Alacritech

AMD

B

BakBone

BCM

Böwe Bell & Howell

Bridgeworks

Brocade

C

Canon

Chenbro

Chi Mei

Chip PC

Cisco

Control Europe

Crossroads

D

Datamax

Decru / NetApp

Dot Hill

E

eCopy

EIZO

EMC-Captiva

Emerson/Motorola

Emulex

Enterasys Networks

Ericom

Esker

Expand Networks

F

F5 Networks

Fibrenetix

Fuji

Fujitsu

G

GRAU DATA

H

H+H Software

Honeywell

Hitachi

HP

HP / Lefthand

I

IBM

IDTech

InfoPrint Solutions
Company

Intel

Intermec

iTernity

Itox

K

Kingston

Kodak

Kofax

L

LG

M

Matrox

Micron

Motorola/Emerson

Motorola Enterprise Mobility
(Symbol)

N

Nanya

NetApp

Neterion

NSi

NTP Software

O

O'Neil

Overland

P

Panasonic

Powertip

Q

QLogic

Qstar

Quantum (Adic)

R

Ruckus Wireless

S

Samsung

Sapphire

Scan-Optics

Seagate/Maxtor

Sharp

Silex Technology

SmartOptics

StorLife

Supermicro

T

tecmasters

ThinPrint

Toshiba

Transcend

Transition Networks

Trapeze Networks

U

UniCon

V

Visioneer

VXL

W

Wyse

X

XFX

Xsigo Systems

Avnet bietet Ihnen Produkte und **Lösungen** in allen relevanten Bereichen

- Computer Components
- Display Solutions
- Document Management Technologies
- Embedded Computing
- Networking & Security
- Server & Infrastructure Solutions
- Server Based Computing / Thin Clients
- Services
- Software
- Storage & SAN
- Unified Communications
- Virtualisation
- Wireless & Mobility

Avnet Technology Solutions GmbH
Lötscher Weg 66
D-41334 Nettetal
T +49 (0)2153 733-0
F +49 (0)2153 733-110
ats.de@avnet.com

www.ts.avnet.com/de

